

# 3-Axis Positioner APL-50kg

The maturo 3-axis APL positioning system is especially designed for antenna measurements in near-field or far-field.




Fig.: Principle build-up of Positioner

# Features:

- Used for antenna measurements
- Independent rotations azimuth and polarisation
- Variable speed adjustments at all axes
- Possibility of operation in manual, semi-automatic and simultaneous remote control mode via IEEE 488.2 (GPIB bus) with the controller NCD using fibre optic control
- Readout by high accurate encoders
- Use of reliable, long-lasting and maintenance-free bearings
- Integrated rotary joint for power supply of EUT available upon request
- Easy installation in existing chambers



info@maturo-gmbh.de www.maturo-gmbh.de



# **Specifications:**

# **Azimuth Positioner**

Fixed directly onto Groundplane of chamber		
Diameter 900	mm	
Operation load capability 50 k	٨g	
Bending Moment 500	Nm	
Rotating speed adjustable up to 5 rp	m	
Rotating angle ± 18	30°	
Positioning accuracy $\pm 0$ .	05°	
Repeatability 0.02	<u>2</u> °	

# **Polarisation Positioner**

Height of rotation axis Diameter of mounting plate Operation load capability Bending Moment Rotating speed adjustable up to Rotating angle Positioning accuracy Repeatability

# **Linear Positioner**

Fixed to the azimuth Positioner Operation load capability Movement range Positioning accuracy

50 kg 500 mm +/- 0.5 mm

1.5 m

50 ka

5 rpm

± 180°

± 0.05°

0.02°

400 mm

500 Nm

Motor Drive unit

Control cable Remote control via Current consumption Voltage Temperature range Material of structure Total weight Brushless stepper motors 200 W shielded and radio interference suppressed under EN 55022 class B

Fibre optic lines IEEE interface max. 32A 380-400 VAC, 50/60 Hz, 3-phase +5 °C...+35 °C Aluminium approx. 340 kg

# **Brief description**

The Device **APL-50kg** is especially designed for antenna measurements and tests. Different sized of antennas can be mounted on the rotating plate.

The polarisation positioner is mounted onto the azimuth positioner to have both 360° vertical and horizontal rotation for 3D measurements. The system performs three-dimensional over-the-air radiation measurements.

Phone: +49 (0)9606 923913-0 Fax: +49 (0)9606 923913-29





# **Controller NCD**

The new developed Multiple Control Device **NCD** is suited for the operation of up to 8 devices with multiple axis of motion. Those devices can be any combinations of antenna masts, turntables, cable guide rails or any other positioning equipment.

This controller NCD permits the operation in manual, semi-automatic and remote control mode via IEEE 488.2 (GPIB bus), or optionally other interfaces, of multiple devices simultaneously.



Figure: NCD with option "tip-up handle"

Technical Data		
Data interfaces		IEEE 488.2 (GPIB-Bus) and Ethernet (Optional available: USB, RS232, etc.)
Transmission		Fibre optic cable (up to 2000 m distance)
Transfer rate		Real time 100 Mbit/s (fast Ethernet)
Display		5.7" TFT Touch screen-Display
Voltage Current consumption	approx	100-240 VAC, 50/60 Hz, single phase , 70W
Fuse		T 0.63A
Size (W X D)		19" Rack mount and table unit (427 x 300 mm) (Optional with tip-up carry handle)
Height		3 HE (133 mm)
Temperature range Total weight	approx	5°C - 40°C . 8 kg
Accessories		1.5 m power supply cable, Service manual



# **Brief description of NCD**

The multiple control device NCD works with Agilent, Rohde & Schwarz, Teseq and other software. The IEEE 488 (GPIB) is available as a standard interface device. Other interfaces available upon request.

- User-friendly, time-saving function keys

The function keys F1 to F10 allows the implementation of individual, customerspecific sequence programs for user-friendly, times-saving handling and operation. The individual programs can be stored and accessed by one function key.

Error analysis based on error codes
Diagnosis via USB interface possible
Optional analysis via internet and Ethernet interface possible

# - USB interface

Updates easily implemented by USB stick Possibility to plug in a computer mouse and keyboard

# - Easy operation with touch panel

Fast and reliable operability based on touch panel technology Layout of touch screen display can easily be adjusted according to customers' request

# - Position keys

With the position keys Up/DOWN, CW/CCW and VER/HOR the Positioners can easily be moved in manual mode.

# - Real-time capable

Each program cycle will finished in the default time frame be no matter how many devices are controlled at the same time. Due to this feature no overflow of commands can happen when using fast remote computers.

# - Handheld control unit

Easy implementation of standard or customer-specific handheld control units possible

# - Precise Display Accuracy

The display resolution is highly precise with position readout increments of 0.1 mm respectively 0.01 degree.

Information presented enclosed is subject to change as product enhancements are made regularly. Pictures included are for illustration purposes only and do not represent all possible configurations.